

Company with Quality System in accordance with ISO 9001: 2015 **Certified by Bureau Veritas**

Technical data sheet

Total thickness (carrier + adhesive): **0.55** mm

BS MOUNT 20.275 TT

Main carrier:	GREY PE FOAM
Secondary carrier:	TRANSPARENT REINFORCEMENT FILM
Main liner:	TRANSPARENT SILICONE ORANGE PEEL EMBOSSED PP FILM
Secondary liner:	-
Open side adhesive:	NATURAL RUBBER
Closed side adhesive:	NATURAL RUBBER

Adhesive properties

Peel 90° on steel		Open side	6	M.U.	Method
		Closed side	10	N/25 mm	BS 35 - AFERA 5001
Rolling ball test		Open side	1	M.U.	Method
		Closed side	1	Cm	BS 12 - PSTC-6
Quick stick on steel		Open side	8	M.U.	Method
		Closed side	10	N/25 mm	BS 6 - AFERA 4015
Shear on steel	KG	Open side	60	M.U.	Method
		Closed side	60	Hours	BS 254

Temperature resistance

Long term	+5°/+60°	M.U.: °C
Short term	+5°/+80°	M.U.: °C

Mechanical properties

Tensile strength at break Longitudinal	Z O	Min. 9380	Max. 9380	M.U. kPa	Method ISO-1926
Tensile strength at break Transversal		Min. 8990	Max. 8990	M.U. kPa	Method ISO-1926
Elongation at break Longitudinal	3	Min. 44	Max. 44	M.U.: %	Method ISO-1926
Elongation at break Transversal		Min. 41	Max. 41	M.U.: %	Method ISO-1926



Company with Quality System in accordance with ISO 9001: 2015 Certified by Bureau Veritas

Technical data sheet

Total thickness (carrier + adhesive): **0.55 mm**

BS MOUNT 20.275 T

Description

The product is made up of a laminated multi-layer, calibrated thickness, closed cell polyethylene, physically reticulated, foam carrier and a transparent orange peel embossed polypropylene silicone film liner. On one side, the PE foam carrier is reinforced with a transparent film.

The natural rubber adhesive system (wet-style), on both sides, provides very high adhesion performances.

Low compressibility, identified through the grey coloured foam..

Applications

Ideal for Wide Web flexo printing of flexible packaging material.

Suitable for full solid print.

Recommended for medium and high thickness photopolymer plates.

Ideal for mounting operations on steel and aluminium cylinders.

Optimal printing results at very high speed and long printing runs.

Product PLUS

The surface structure of the liner is especially designed to impress undulations in the adhesive for the potential exit of air bubbles trapped between the double-side adhesive tape and the cylinder or the plate during mounting operations.

High resilience foam

High adhesion level, ideal for maximum hold on either plates or cylinders, especially in edge to edge plate mounting operations.

Recommendations for correct use

For a proper storage of the product we recommend to keep the product in the original package until it is needed and use it within 12 months from delivery.

The storage shall be carried out at a room temperature between 15°C and 25°C, and a relative humidity < 65%.

Once removed from the packaging, place the product vertically and protect it from dust. Do not expose product and packaging to direct sunlight and heat sources.

Surface cleaning The product shall be applied on sufficiently flat surfaces and with no non-stick coating.

In order to obtain a correct product adhesion level on surfaces, it is indispensable that the surfaces are properly cleaned before the application. It is recommended to use quick-evaporating solvents.

After cleaning make sure that the solvent has completely evaporated, by waiting for a sufficiently long period of time or by drying the surface with a completely dry cloth.

Application

As adhesive tape is pressure-sensitive, it is necessary a proper pressing pressure on the back of the tape, once applied on the surface, to ensure the grip of the adhesive and a full lamination.

Measuring tolerances

The tape cutting width tolerance can vary within a range of ±2.0 mm. Different tolerances for specific formats and measures can be available on request.

Disposal

It is recommend to dispose the product after use according to the specific regulations of the country it was used in.

For additional information, please refer to our Technical Office: info.tapes@biesSseworld.com +39 02 90 11 11 18

MOD. 003-A - Rev.7 del 09/27