





Technical data sheet

Total thickness (carrier + adhesive): **1.20 mm**



# MS FOAM 1100 SA RED

Main carrier:	RED PE FOAM
Secondary carrier:	-
Main liner:	WHITE SILICONE GLASSINE PAPER
Secondary liner:	-
Open side adhesive:	-
Closed side adhesive:	PURE ACRYLIC





**Adhesive properties**

<b>Peel 90° on steel</b>		Open side	-	M.U.	Method
		Closed side	<b>4.5</b>	N/25 mm	BS 35 - AFERA 5001
<b>Rolling ball test</b>		Open side	-	M.U.	Method
		Closed side	<b>2</b>	Cm	BS 12 - PSTC-6
<b>Quick stick on steel</b>		Open side	-	M.U.	Method
		Closed side	<b>9</b>	N/25 mm	BS 6 - AFERA 4015
<b>Shear on steel</b>		Open side	-	M.U.	Method
		Closed side	<b>15</b>	Hours	BS 254

**Temperature resistance**

<b>Long term</b>		-	M.U.: °C
<b>Short term</b>		-	M.U.: °C

**Mechanical properties**

<b>Tensile strength at break Longitudinal</b>		Min.	Max.	M.U.	Method
		<b>2.2</b>	<b>2.2</b>	N/mm2	ISO 1798
<b>Tensile strength at break Transversal</b>		Min.	Max.	M.U.	Method
		<b>1.3</b>	<b>1.3</b>	N/mm2	ISO 1798
<b>Elongation at break Longitudinal</b>		Min.	Max.	M.U.: %	Method
		<b>304</b>	<b>304</b>		ISO 1798
<b>Elongation at break Transversal</b>		Min.	Max.	M.U.: %	Method
		<b>327</b>	<b>327</b>		ISO 1798

Note: All above information are believed to be true and reliable but they are given only for guidance. They do not constitute a warranty or a specification. The characteristics refer to average values, relevant to samples collected from our production. Users must confirm the suitability of the products through their own tests. BiesSse Tape reserve the right to introduce at any moment and without warning those changes that they deem necessary. Tolerance of Technical Data: ± 30%

## Technical data sheet

Total thickness (carrier + adhesive): **1.20 mm**

# MS FOAM 1100 SA RED

### Description

The product is made up of a high quality red closed-cell expanded polyethylene foam carrier and a white silicone glassine paper liner.

Foam and paper width: 1200 mm

### Applications

Ideal for high quality corrugated post-print and for pre-mounting on PET sheets in flexographic printing.

Reccomended to reduce "dot gain" and "washboard" effects.

Suitable for different plate thicknesses and for equalizing the thickness of "undercut" on the cylinder.

### Product PLUS

Excellent slipping on the printing cylinder.

Optimal resilience and high compression stability even at high print speeds to avoid cardboard crushing.

## Recommendations for correct use

### Storage

For a proper storage of the product we recommend to keep the product in the original package until it is needed and use it within 12 months from delivery.

The storage shall be carried out at a room temperature between 15°C and 25°C, and a relative humidity < 65%.

Once removed from the packaging, place the product vertically and protect it from dust. Do not expose product and packaging to direct sunlight and heat sources.

### Surface cleaning

The product shall be applied on sufficiently flat surfaces and with no non-stick coating.

In order to obtain a correct product adhesion level on surfaces, it is indispensable that the surfaces are properly cleaned before the application. It is recommended to use quick-evaporating solvents.

After cleaning make sure that the solvent has completely evaporated, by waiting for a sufficiently long period of time or by drying the surface with a completely dry cloth.

### Application

As adhesive tape is pressure-sensitive, it is necessary a proper pressing pressure on the back of the tape, once applied on the surface, to ensure the grip of the adhesive and a full lamination.

### Measuring tolerances

The tape cutting width tolerance can vary within a range of  $\pm 2.0$  mm. Different tolerances for specific formats and measures can be available on request.

### Disposal

It is recommend to dispose the product after use according to the specific regulations of the country it was used in.

For additional information, please refer to our Technical Office:  
**info.tapes@biesSseworld.com**  
**+39 02 90 11 11 18**